







| A | Skin | Size |
|---------|---|--|
| |  | 38.5" W x 38.5" H |
| Diamond | | Diamond Shown as it will appear on the Xpressions unit |

| B | Skin | Size |
|---------|---|--|
| |  | 38.5" W x 38.5" H |
| Diamond | | Diamond Shown as it will appear on the Xpressions unit |


| C | Skin | Size |
|------------------|--|---|
| |  | 28.5" W x 28.5" H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| D | Skin | Size |
|------------------|---|---|
| |  | 28.5" W x 28.5" H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| E | Skin | Size |
|------------------|---|---|
| |  | 28.5" W x 28.5" H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| F | Skin | Size |
|------------------|---|---|
| |  | 28.5" W x 28.5" H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

It is recommended that all text and borders be 2" from the finish size



Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details